



# AutoStrain RV eLearning

AutoStrain RV eLearning - AutoStrain RV provides simple and fast RV Global Strain through Auto View Recognition and labeling, Auto Contour Placement and fast speckle tracking. The tool also provides RV Free Wall Strain. This eLearning will review the features and workflow of the AutoStrain RV tool.

The AutoStrain RV eLearning module will:

- Describe the benefits of AutoStrain RV on the EPIQ ultrasound system
- Review the steps essential to AutoStrain RV workflow
- Describe the steps needed to edit a tracing in AutoStrain RV

This course is intended for customers who have purchased the AutoStrain RV options.

This ASRT-accredited module is a self-paced tutorial consisting of enlightening content and colorful images.



### For more information

Contact a Philips ultrasound clinical services coordinator at 800-522-7022 and visit our education catalog at

[www.learningconnection.philips.com/ultrasound](http://www.learningconnection.philips.com/ultrasound)